



## Angle grinder Cordless, Type: M18FHSAG55



### Order data

Order number	077140 M18FHSAG55
GTIN	4058546287078
Item class	03L

### Description

#### Version:

18 V / 5.0 Ah FUEL™ Milwaukee cordless angle grinder:

- **long-life brushless motor, spindle locking, quick adjustment of the safety guard.**
- **Integral FIXTEC quick-release system for changing discs without using tools.**

M18™ **HIGH-OUTPUT™ 125 mm cordless angle grinder** with enough power for roughing and for up to 145 cuts per charge (5.5 Ah) with 50-mm electric pipe. RAPIDSTOP™ brake stops disc in under 2.5 seconds.

#### Supplied with:

Supplied with 2× M18 HB5.5 battery packs, M12-18 FC charger, HD box.

#### Note:

See from No. 073809 and No. 073840 for suitable replacement batteries and accessories.

### Technical description

suitable battery - supplier / battery type / voltage	Milwaukee type B 18 V
suitable battery - supplier / battery type / voltage	Milwaukee type HB 18 V
Weight	3.4 kg
Number of rechargeable batteries contained	1
maximum vibration to EN	3.4 m/s <sup>2</sup>
Restart block	yes
maximum cutting depth	33 mm

maximum disc Ø	125 mm
maximum speed	9000 min <sup>-1</sup>
Manufacturer's designation	M18FHSAG125XB-552X
Kick-back stop	yes
Battery capacity	5.5 Ah
Battery voltage	18 V
Type of rechargeable battery	Lithium-ion
Overload protection	yes
Dead man's circuit	no
Soft start	yes
Packaging	Modular case (HD=Heavy Duty)
Power supply	Rechargeable battery-powered
Series	FUEL
Type of product	Angle grinder

## Accessories

Battery starter set Type M18NRG5	073839 M18NRG5
Li-ion batteryHigh Output™ Battery type MHB8	073810 MHB8
Li-ion system M18B2 Battery type MB18	073827 MB18
Battery starter setHigh Output™ Type M18HNRG55	073830 M18HNRG55
Li-ion batteryHigh Output™ Battery type MHB12	073811 MHB12
Li-ion batteryHigh Output™ Battery type MHB55	073809 MHB55
Li-ion system M18B5 Battery type MB18	073816 MB18
Battery starter setHigh Output™ Type M18HNRG12	073833 M18HNRG12
Battery starter setHigh Output™ Type M18HNRG8	073831 M18HNRG8
Li-ion batteryHigh Output™ Battery type MHB3	073808 MHB3
Battery starter setHigh Output™ Battery type M18HNRG3	073826 M18HNRG3