



## Pneumatic drill, Type: D2148RQ



### Order data

Order number	079051 D2148RQ
GTIN	7322590019785
Item class	03R

### Description

#### Version:

All technical data relate to a dynamic pressure of **6.3 bar** and the specified hose internal  $\varnothing$ . A range of powerful and very smooth running drills with pistol grip and a drilling power of up to 13 mm in steel. Exhaust air is discharged through the handle, to prevent drill chips from swirling up. With quick-release chuck. With changeover valve for **clockwise / anticlockwise rotation** (for use as a screwdriver or tap driver).

#### Supplied with:

**Quick-clamping chuck.** Additionally with support handle.

#### Spare part:

**Selected service kits:** Sets of replacement parts for most Atlas Copco pneumatic tools can be supplied on request for preventive maintenance and servicing.

### Technical description

Quick-clamping chuck range	1.5 - 13 mm
maximum air consumption	600 l/min
maximum speed	0 - 750 min <sup>-1</sup>
maximum vibration to EN	3.7 m/s <sup>2</sup>
Length	248 mm
Output power	250 W

Weight	1.4 kg
recommended hose size (internal Ø)	10 mm
Operating noise	85 dB(A)
Manufacturer's designation	D2148RQ
Compressed air connection	1/4 in
Connection thread	BSP
Type of product	Drill