



PTFE dry lubrication spray, Contents: 200ml



Order data

Order number	083051 200
GTIN	4017777256000
Item class	08E

Description

Version:

When sprayed on, very fine PTFE particles achieve clean dry lubrication without oily hands and stubborn dirt, coupled with effective reduction in adhesive friction, sliding friction and rolling friction.

Advantage:

- **Hygienic lubrication of dry and solid materials.**
- **No adhesion of dirt or dust to the treated surface.**
- **No subsequent annoying lubricant slime.**
- **Without oil or grease components.**
- **Hygienic, clean and environmentally compatible.**
- **Sustained and persistent improvement in lubrication and sliding properties.**
- **Free of resin, does not gum up.**
- **High material compatibility (with all metal and plastic parts!).**
- **Contains no silicones and or acids.**

Application:

- **In sensitive areas such as handling textiles or paper with high dust levels.**
- **To reduce the friction on rollers and bearings, slides and guide rails, rope lifting gear and telescopic guides, drives and gear wheels together with all kinds of plastics.**

- **The adhesive friction of PTFE is exactly the same as the sliding friction, so there is no jerk when starting into movement from a stationary position.**

Technical description

Labelling of hazardous substances	GHS02: Flame
Labelling of hazardous substances	GHS07 caution
Colour	transparent
Flashpoint	-104 °C
Spray head	Standard
Spontaneous ignition temperature	400 °C
Boiling point	78 °C
Solubility in water	insoluble
Version	Spray can
Contents	0.2 l
Type of product	Lubricant