

Garant GRIDLINE

Base cabinet for measuring microscopes, width×depth: 1500X700mm**Order data**

Order number	492580 1500X700
GTIN	4062406279929
Item class	41M

Description**Version:**

Body of welded sheet steel, with bench top of Eluplan dark grey, edges veneered with 3 mm thick graphite. Incorporating the GARANT locking system.

Suitable for:

GARANT video measuring microscopes with measuring range max. X=200 / Y=100.

Fitted with:

Drawer front height (left): 50; 300; 300 mm

Colour:

Body light grey RAL 7035, drawers anthracite grey RAL 7016.

Technical description

Drawer usable depth	500 mm
Load capacity, distributed	1000 kg
Number of drawers	3
Depth	700 mm
Drawer usable width	500 mm
Width	1500 mm
Weight	124 kg

Workbench height	840 mm
Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension	100
Hoffmann perforated panel grid interval	9×9
Cylinder lock	modular barrel
Type of product	Sub-frame