

Garant GRIDLINE

**Base cabinet for measuring microscopes, width×depth: 1800X900mm****Order data**

Order number	492580 1800X900
GTIN	4062406279936
Item class	41M

**Description****Version:**

Body of welded sheet steel, with bench top of Eluplan dark grey, edges veneered with 3 mm thick graphite. Incorporating the GARANT locking system.

**Suitable for:**

GARANT video measuring microscopes with measuring range X=300 / Y=200.

**Fitted with:**

Drawer front height (left): 50; 300; 300 mm

**Colour:**

Body light grey RAL 7035, drawers anthracite grey RAL 7016.

**Technical description**

Weight	188 kg
Drawer usable width	500 mm
Drawer usable depth	500 mm
Width	1800 mm
Load capacity, distributed	1000 kg
Depth	900 mm
Number of drawers	3
Workbench height	840 mm

Drawer/pull-out shelf load capacity	75 kg
Insert thickness	50 mm
Drawer runner extension	100
Hoffmann perforated panel grid interval	9×9
Cylinder lock	modular barrel
Type of product	Sub-frame