


**VHB™ adhesive tape, black, Width×length (mm× m): 25X33****Order data**

Order number	083789 25X33
GTIN	4001895844928
Item class	08M

Description**Version:**

Double-sided high-performance **adhesive tape** of pure acrylate adhesive (VHB) for permanently strong bonds. High instant tack, high resistance to temperature, weather, UV and solvents. Excellent sealing function, vibration-damping.

The **3M™ 5952** is suitable for use indoors and outdoors. It can be applied quickly and easily, and provides a high-performance and permanent bond. Use this high-performance and visco-elastic VHB adhesive tape on a wide variety of surfaces such as powder coating paint finishes.

Note:

Further 3M™ VHB™ tapes in different thicknesses and lengths are available on request.

The specified "best before" date for 3M™ products is in relation to compliance with the specified storage guidelines.

Technical description

Width	25 mm
Storage temperature	20 °C
Manufacturer's designation	5952
Thickness	1.1 mm
Material of covering	Siliconised PE film
Type of adhesive tape	double-sided

Adhesive strength on steel	5.5 N/mm
Adhesive	Acrylate
Stretch capability	300 %
"Best before" date	12 mo
Length	33 m
Storage humidity	50 %
Colour	grey
Product name attribute	black
Type of product	Adhesive tape