

3M**VHB™ adhesive tape, black, Width×length (mm× m): 12X33**

Order data

Order number	083782 12X33
GTIN	4001895872778
Item class	08M

Description

Version:

Double-sided high-performance **adhesive tape** of pure acrylate adhesive (VHB) for permanently strong bonds. High instant tack, high resistance to temperature, weather, UV and solvents. Excellent sealing function, vibration-damping.

The **3M™ 5952** means reliability right across the board. It offers optimum adaptability to the surfaces to be bonded. This feature permits even thin and structured surfaces to be joined without any sort of stress.

Note:

The specified "best before" date for 3M™ products is in relation to compliance with the specified storage guidelines.

Further 3M™ VHB™ tapes in different thicknesses and lengths are available on request.

Adhesive: Acrylate

Length: 33 m

Width: 12 mm

Thickness: 1.6 mm

Technical description

Adhesive	Acrylate
Material of covering	Paper
Type of adhesive tape	double-sided
"Best before" date	12 mo
Colour	grey
temperature-resistant up to	120 - 150 °C
Storage humidity	50 %
Width	12 mm
Application	Sealing
Application	Masking
Application	Assembly
Application	Attaching
Storage temperature	20 °C
Adhesive strength on steel	5.5 N/mm
Length	33 m
Special features	damping
Special features	moisture-resistant
Special features	clings well
Thickness	1.6 mm
Stretch capability	300 %
Manufacturer's designation	5962F
Product name attribute	black
Type of product	Adhesive tape