



## Shell jacket OXFORD, black, Unisex size: M



### Order data

Order number	090684 M
GTIN	7040055730203
Item class	09L

### Description

#### Version:

The Oxford range from Helly Hansen offers high-quality lightweight work clothing. The **modern design** of the collection is impressive.

Versatile and **light shell jacket** with breathable Helly Tech® performance membrane provides the wearer with reliable protection against wet, even under the most adverse conditions.

The **adjustable seams** with elasticated pull cord ensure a **good fit**. The optimum freedom of movement and the outstanding wearing comfort are achieved due to the **pre-shaped sleeves and the extended back**.

- **Removable hood with pull cord and catch.**
- **No shoulder seams.**
- **YKK® front zip fastener with chin protection.**
- **Brushed polyester on the inside of the collar.**
- **Side document pockets with YKK® zip fasteners.**
- **Internal breast pocket.**
- **Wind protection at the front.**

#### Standard:

Versatile and **light shell jacket** with breathable Helly Tech® performance membrane provides the wearer with reliable protection against wet, even under the most adverse conditions.

The **adjustable seams** with elasticated pull cord ensure a **good fit**. The optimum freedom of

movement and the outstanding wearing comfort are achieved due to the **pre-shaped sleeves and the extended back.**

- **Removable hood with pull cord and catch.**
- **No shoulder seams.**
- **YKK® front zip fastener with chin protection.**
- **Brushed polyester on the inside of the collar.**
- **Side document pockets with YKK® zip fasteners.**
- **Internal breast pocket.**
- **Wind protection at the front.**

Washing: 40 °C coloureds

## Technical description

Series	OXFORD
Unisex size	M
Fabric composition	100% polyester
Material weight / fabric density	255 g/m <sup>2</sup>
Clothing standard	Oeko-Tex Standard 100
Washing	40 °C coloureds
Colour	black
Type of product	Soft shell jacket