

SONO  SWISS<sup>®</sup>**DURA-T ultrasonic cleaning unit, Capacity: 30l****Order data**

Order number	082924 30
GTIN	2050002040380
Item class	04E

**Description****Version:**

Units of drawn or welded stainless steel. Temperature control from 30 °C to 80 °C in 5 °C steps. Bench-top device: DURA-T – welded DUPLEX stainless steel baths suitable for multi-shift operation.

**Application:**

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaners depending on the dirt and effectiveness required (from No. 082930). The component to be cleaned must be completely surrounded by cleaning fluid.

**Supplied with:**

Ultrasonic cleaning unit with cover, without basket (No. 082926).

**Note:**

Further sizes and types on request.

Component basket can be found under No. 082926 in the online shop.

**Technical description**

Cleaning bath height	200 mm
Extension option oil separator	no
Item height	320 mm

Item width	355 mm
Extension option rinsing module	no
Cleaning bath length	570 mm
Extension option drying module	no
Item length	570 mm
Heating power	1200 W
Extension option pump filtration	no
Cleaning bath width	330 mm
Capacity of cleaning bath	30 l
Maximum ultrasonic power	1200 W
Weight	11.2 kg
Power consumption	1500 W
Nominal voltage	230 V
Power supply	Mains-powered
Width of component basket	238 mm
Length of component basket	443 mm
Nominal contents	20.6 l
Type of product	Ultrasonic cleaning unit

## Accessories

Ultrasonic power cleanerT2 Capacity l/kg 2,5	082932 2,5
Ultrasonic power cleanerT1 Capacity l/kg 2,5	082930 2,5
Corrosion protection Capacity l/kg 1	082931 1
Ultrasonic power cleanerT5 Capacity l/kg 10	082935 10
Corrosion protection Capacity l/kg AK	082931 AK
Ultrasonic power cleanerT2 Capacity l/kg 10	082932 10
Component basket INOX Size suitable for No. 082922 / 082923 / 082924 30	082926 30

Ultrasonic power cleanerT4 Capacity l/kg 2,5	082934 2,5
Ultrasonic power cleanerT1 Capacity l/kg 10	082930 10
Ultrasonic power cleanerT4 Capacity l/kg 10	082934 10