

SONO  SWISS[®]**DURA-T ultrasonic cleaning unit, Capacity: 12l****Order data**

Order number	082924 12
GTIN	2050002040366
Item class	04E

Description**Version:**

Units of drawn or welded stainless steel. Temperature control from 30 °C to 80 °C in 5 °C steps. Bench-top device: DURA-T – welded DUPLEX stainless steel baths suitable for multi-shift operation.

Application:

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaners depending on the dirt and effectiveness required (from No. 082930). The component to be cleaned must be completely surrounded by cleaning fluid.

Supplied with:

Ultrasonic cleaning unit with cover, without basket (No. 082926).

Note:

Further sizes and types on request.

Component basket can be found under No. 082926 in the online shop.

Technical description

Item length	355 mm
Cleaning bath width	238 mm
Capacity of cleaning bath	12 l

Cleaning bath length	297 mm
Maximum ultrasonic power	800 W
Extension option drying module	no
Item height	320 mm
Item width	290 mm
Heating power	800 W
Extension option oil separator	no
Extension option pump filtration	no
Cleaning bath height	200 mm
Extension option rinsing module	no
Weight	7.3 kg
Length of component basket	240 mm
Power consumption	1000 W
Power supply	Mains-powered
Width of component basket	181 mm
Nominal voltage	230 V
Nominal contents	9 l
Type of product	Ultrasonic cleaning unit

Accessories

Ultrasonic power cleanerT1 Capacity l/kg 10	082930 10
Ultrasonic power cleanerT4 Capacity l/kg 10	082934 10
Corrosion protection Capacity l/kg 1	082931 1
Corrosion protection Capacity l/kg AK	082931 AK
Ultrasonic power cleanerT2 Capacity l/kg 10	082932 10
Ultrasonic power cleanerT4 Capacity l/kg 2,5	082934 2,5
Ultrasonic power cleanerT5 Capacity l/kg 10	082935 10
	082926 12

Component basket INOX Size suitable for No. 082922 /
082923 / 082924 12

Ultrasonic power cleanerT2 Capacity l/kg 2,5	082932 2,5
Ultrasonic power cleanerT1 Capacity l/kg 2,5	082930 2,5