

SONO  SWISS<sup>®</sup>**DURA-T ultrasonic cleaning unit, Capacity: 18l****Order data**

Order number	082924 18
GTIN	2050002040373
Item class	04E

**Description****Version:**

Units of drawn or welded stainless steel. Temperature control from 30 °C to 80 °C in 5 °C steps. Bench-top device: DURA-T – welded DUPLEX stainless steel baths suitable for multi-shift operation.

**Application:**

For removal of oil, grease, grinding fluids, polishing fluids, paint residues, flux, oxide layers, carbon deposits, scale from nearly all surfaces and even from inaccessible places, whilst treating the component being cleaned with the utmost care. Use special power cleaners depending on the dirt and effectiveness required (from No. 082930). The component to be cleaned must be completely surrounded by cleaning fluid.

**Supplied with:**

Ultrasonic cleaning unit with cover, without basket (No. 082926).

**Note:**

Further sizes and types on request.

Component basket can be found under No. 082926 in the online shop.

**Technical description**

Heating power	800 W
Maximum ultrasonic power	800 W
Extension option drying module	no

Extension option pump filtration	no
Item length	386 mm
Extension option oil separator	no
Capacity of cleaning bath	18 l
Cleaning bath width	300 mm
Item width	355 mm
Weight	8.7 kg
Extension option rinsing module	no
Item height	320 mm
Cleaning bath height	200 mm
Cleaning bath length	330 mm
Nominal voltage	230 V
Length of component basket	267 mm
Power supply	Mains-powered
Width of component basket	241 mm
Power consumption	1000 W
Nominal contents	12.9 l
Type of product	Ultrasonic cleaning unit

## Accessories

Ultrasonic power cleanerT2 Capacity l/kg 2,5	082932 2,5
Ultrasonic power cleanerT4 Capacity l/kg 2,5	082934 2,5
Ultrasonic power cleanerT5 Capacity l/kg 10	082935 10
Ultrasonic power cleanerT1 Capacity l/kg 2,5	082930 2,5
Ultrasonic power cleanerT2 Capacity l/kg 10	082932 10
Corrosion protection Capacity l/kg AK	082931 AK
Ultrasonic power cleanerT1 Capacity l/kg 10	082930 10
Corrosion protection Capacity l/kg 1	082931 1

Ultrasonic power cleanerT4 Capacity l/kg 10

082934 10