

Garant

Shoe, anthracite/black Comfort ESD S1P W2 safety shoes, EU shoe size: 41



Order data

Order number	092059 41
GTIN	4062406280536
Item class	01S

Description

Version:

GARANT comfort safety shoes combine the highest possible wearing comfort with modern design. Innovative and high-quality materials coupled with very high-quality workmanship "Made in Germany" guarantee very high protection combined with minimum weight. Different calf widths (width W1 for normal width feet, width W2 for wider feet) and the tweaked manufacturing technique permits a "true" multi-width system and thus create an ideal solution to the requirement for different widths of feet. The rigorous implementation of ergonomic principles and exchangeable weight-dependent damping significantly reduce the stresses on the knee and back, and thus contribute appreciably to long-term health.

- **The material of the uppers is light-weight but hard-wearing micro-fibre.**
- **Breathable functional lining.**
- **Practical GARANT comfort heel-puller allows the shoes to be taken off quickly and easily.**
- **GARANT comfort insoles with weight-dependent damping.**
- **Outer sole GARANT comfort TPU**
- **Protection against electrostatic discharge (ESD).**

Shoe with large area ventilation structure and textile penetration protection.

Standard:

EN ISO 20345:2011 S1 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Note:

- **GARANT See accessories for foot protection for the comfort insoles with weight-dependent damping, under: 092864 (soft), 092865 (medium), 092866 (hard).**

- **Shoes of sizes 36-39 are supplied as standard with soft damping, sizes 40-45 with medium damping and sizes 46-48 with hard damping.**
- **See accessories for foot protection for the appropriate GARANT shoelaces under: 092855 120.**

electrostatic characteristic: EGB/ESD

Protection class: S1P

Material of protective toe-cap: Aluminium

Puncture resistance: Tekstil

Standard: Inlay type-tested according to DGUV regulation 191

Characteristics: Vario® damping

Technical description

Standard	Inlay type-tested according to DGUV regulation 191
Material of protective toe-cap	Aluminium
EU shoe size	41
Puncture resistance	Tekstil
Characteristics	Vario® damping
Gender	Unisex
Protection class	S1P
electrostatic characteristic	EGB/ESD
Type of product	Safety shoes

Accessories

Insoles, anthracite Comfort insole, SOFT EU shoe size 41	092864 41
Insoles, anthracite Comfort insole, MEDIUM EU shoe size 41	092865 41
Insoles, anthracite Comfort insole, HARD EU shoe size 41	092866 41