

Garant

Shoe, anthracite/black Comfort ESD S3 W2 safety shoes, EU shoe size: 47



Order data

Order number	092071 47
GTIN	4062406281113
Item class	01S

Description

Version:

GARANT comfort safety shoes combine the highest possible wearing comfort with modern design. Innovative and high-quality materials coupled with very high-quality workmanship "Made in Germany" guarantee very high protection combined with minimum weight. Different calf widths (width W1 for normal width feet, width W2 for wider feet) and the tweaked manufacturing technique permits a "true" multi-width system and thus create an ideal solution to the requirement for different widths of feet. The rigorous implementation of ergonomic principles and exchangeable weight-dependent damping significantly reduce the stresses on the knee and back, and thus contribute appreciably to long-term health.

- **The material of the uppers is light-weight but hard-wearing micro-fibre.**
- **Breathable functional lining.**
- **Practical GARANT comfort heel-puller allows the shoes to be taken off quickly and easily.**
- **GARANT comfort insoles with weight-dependent damping.**
- **Outer sole GARANT comfort TPU**
- **Protection against electrostatic discharge (ESD).**

Shoe of seam-free construction with textile penetration protection. Dust flap. Protection against water penetration.

Standard:

EN ISO 20345:2011 S3 SRC

Einlagenversorgung baumustergeprüft nach DGUV Regel 191.

Note:

- See accessories for foot protection for the GARANT comfort insoles with weight-dependent damping, under: 092864 (soft), 092865 (medium), 092866 (hard).
- Shoes of sizes 36-39 are supplied as standard with soft damping, sizes 40-45 with medium damping and sizes 46-48 with hard damping.
- See accessories for foot protection for the appropriate GARANT shoelaces under: 092855 120.

electrostatic characteristic: EGB/ESD

Protection class: S3

Material of protective toe-cap: Aluminium

Puncture resistance: Tekstil

Standard: Inlay type-tested according to DGUV regulation 191

Characteristics: Vario® damping

Technical description

Protection class	S3
Characteristics	Vario® damping
EU shoe size	47
Standard	Inlay type-tested according to DGUV regulation 191
Puncture resistance	Tekstil
Gender	Unisex
Material of protective toe-cap	Aluminium
electrostatic characteristic	EGB/ESD
Type of product	Safety shoes

Accessories

Insoles, anthracite Comfort insole, SOFT EU shoe size 47	092864 47
Insoles, anthracite Comfort insole, MEDIUM EU shoe size 47	092865 47
Insoles, anthracite Comfort insole, HARD EU shoe size 47	092866 47