

Garant GRIDLINE

**Drawer for sliding door cabinets, Width 30G, 26×14G, Drawer front height: 150mm****Order data**

Order number	940651 150
GTIN	4062406281434
Item class	9GI

**Description****Version:**

Drawers for incorporating in GridLine sliding-door cabinets and roller shutter cabinets. Aluminium handles with labelling strips that can be exchanged and rewritten.

**Suitable for:**

Cabinets No. 940089, No. 940109, No. 940165 – 940237, No. 940885 – 940907.

**Colour:**

Drawer body RAL 7035 light grey, drawer fronts RAL 7016 anthracite, **powder-coated. Drawer body not configurable, always RAL 7035 light grey.**

**Note:**

Cannot be sub-divided using slotted dividers, because the drawer base is solid.

**Technical description**

Weight	15 kg
Usable depth in G	14
Usable width in G	26
Usable height	125 mm
Usable width	650 mm
Usable depth	350 mm
Material thickness	0.9 mm
Drawer/pull-out shelf load capacity	75 kg

Drawer runner extension (partial/full extension)	100 %
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Drawer usable width × usable depth in G	26×14G
Type of product	Drawer

---

## Accessories

Comfort Close drawer closure damping system Load capacity of the drawer 75 kg	950180 75
---	-----------