



## Open ended spanner / ratchet ring spanner reversible 15° offset, Width across flats: 10mm



### Order data

Order number	614905 10
GTIN	3662424064982
Item class	63V

### Description

#### Version:

Drop-forged. Ring and fork with ratchet effect. The additional ratchet mechanism at the open jaws permits quick tightening without having to re-apply the wrench. The ring end has an integral spring to prevent it slipping over the fastener being tightened – reversible for left- and right-hand tightening. Extremely small working arc of 5°.

#### Material:

Chrome vanadium steel, chrome-plated.

### Technical description

Ring $\varnothing$ D	20.2 mm
Jaw width b	22.7 mm
Ring thickness $h_2$	7.3 mm
Width across flats	metric
Spanner length L	158 mm
Jaw height $h_1$	5.1 mm
Width across flats	10 mm
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	chrome-plated

with swivel head	no
Ratchet reversible	yes
Type of product	Spanner