



Open ended spanner / ratchet ring spanner reversible 15° offset, Width across flats: 8mm



Order data

| | |
|--------------|---------------|
| Order number | 614905 8 |
| GTIN | 3662424064968 |
| Item class | 63V |

Description

Version:

Drop-forged. Ring and fork with ratchet effect. The additional ratchet mechanism at the open jaws permits quick tightening without having to re-apply the wrench. The ring end has an integral spring to prevent it slipping over the fastener being tightened – reversible for left- and right-hand tightening. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, chrome-plated.

Technical description

| | |
|-------------------------------|-----------------------|
| Width across flats | metric |
| Jaw width b | 18.6 mm |
| Width across flats | 8 mm |
| Ring Ø D | 16.8 mm |
| Spanner length L | 140 mm |
| Ring thickness h ₂ | 6.5 mm |
| Jaw height h ₁ | 4.6 mm |
| Working arc | 5 degrees |
| Manufacturing process | drop forged |
| Material | Chrome vanadium steel |
| Surface | chrome-plated |

| | |
|--------------------|---------|
| with swivel head | no |
| Ratchet reversible | yes |
| Type of product | Spanner |