



## Open ended spanner / ratchet ring spanner reversible 15° offset, Width across flats: 12mm



### Order data

Order number	614905 12
GTIN	3662424065002
Item class	63V

### Description

#### Version:

Drop-forged. Ring and fork with ratchet effect. The additional ratchet mechanism at the open jaws permits quick tightening without having to re-apply the wrench. The ring end has an integral spring to prevent it slipping over the fastener being tightened – reversible for left- and right-hand tightening. Extremely small working arc of 5°.

#### Material:

Chrome vanadium steel, chrome-plated.

### Technical description

Jaw width b	26.8 mm
Width across flats	12 mm
Spanner length L	171 mm
Jaw height h <sub>1</sub>	5.4 mm
Ring thickness h <sub>2</sub>	8.2 mm
Ring Ø D	23.2 mm
Width across flats	metric
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	chrome-plated

with swivel head	no
Ratchet reversible	yes
Type of product	Spanner