



Open ended spanner / ratchet ring spanner reversible 15° offset, Width across flats: 17mm



Order data

Order number	614905 17
GTIN	3662424065057
Item class	63V

Description

Version:

Drop-forged. Ring and fork with ratchet effect. The additional ratchet mechanism at the open jaws permits quick tightening without having to re-apply the wrench. The ring end has an integral spring to prevent it slipping over the fastener being tightened – reversible for left- and right-hand tightening. Extremely small working arc of 5°.

Material:

Chrome vanadium steel, chrome-plated.

Technical description

Jaw height h_1	6.6 mm
Jaw width b	36.8 mm
Width across flats	metric
Width across flats	17 mm
Ring $\varnothing D$	31.7 mm
Spanner length L	225 mm
Ring thickness h_2	10.3 mm
Working arc	5 degrees
Manufacturing process	drop forged
Material	Chrome vanadium steel
Surface	chrome-plated

with swivel head	no
Ratchet reversible	yes
Type of product	Spanner