



Extendable telescopic precision ratchet, 1/2 inch, Type: 1/2



Order data

Order number	640295 1/2
GTIN	4062406283384
Item class	62A

Description

Version:

Material selection and special forging method guarantee optimal functioning and long life. Fixing is performed by the locking ring. With reversing lever for right-hand and left-hand threads. Extendable from 290 – 430 mm length in 6 stages. **With lockable swivel head and ejector.** Maximum permissible torque 600 Nm.

Standard:

Außenvierkant nach **DIN 3120-A 12,5** mit federnder Kugel.

Suitable for:

Manual use.

Technical description

Square drive	1/2 in
overall length	290 - 430 mm
No. of teeth	72
stepless pull-out	no
Type of product	Ratchet