

Koken
Reversible ratchet, 3/8 inch with ejector, Type: 3/8

Order data

Order number	635050 3/8
GTIN	4991644060580
Item class	63R

Description
Version:

With reversing lever for right-hand and left-hand threads.

Standard:
DIN 3122-D 10

Außenvierkante nach **DIN 3120-A 10** mit federnder Kugel, für Innenvierkante nach **DIN 3120-C 10** mit Rillen.

Material:

Chrome vanadium steel, chrome-plated.

Suitable for :

Manual use.

Square drive: 3/8 inch

No. of teeth: 24

Technical description

Square drive	3/8 inch
Standard	DIN 3120
Standard	DIN 3122
overall length	200 mm
No. of teeth	24
Working angle	15 degrees
Material	Chrome vanadium steel
Surface	chrome-plated

Type of product

Ratchet