



Reversible ratchet, 3/8 inch, Type: 3/8



Order data

Order number	635000 3/8
GTIN	4018754177776
Item class	63A

Description

Version:

With reversing lever for right-hand and left-hand threads.

Standard:

DIN 3122-D 10

Außenvierkant nach **DIN 3120-A 10** mit federnder Kugel, für Innenvierkant nach **DIN 3120-C 10** mit Rillen.

Material:

Chrome alloy steel, chrome-plated.

Suitable for:

Manual use.

Note:

PLEASE NOTE!

An alternative from GARANT is also available for this product.

Recommended product number: 635025

Technical description

Square drive	3/8 in
Standard	DIN 3120
Standard	DIN 3122
overall length	193 mm
No. of teeth	30
Working angle	12 degrees
Material	Chrome alloy steel

Surface	chrome-plated
Type of product	Ratchet