

Garant**Safety hose reel, plastic casing Compressed air, usable hose length: 10m****Order data**

Order number	080078 10
GTIN	4062406284671
Item class	01A

Description**Version:**

- **Safety hose reel with high-impact enclosed plastic casing for use in dirty and dusty environments.**
- **Hose guide and controlled retraction system.**
- **Integral stop ball.**
- **PU hose with high resistance to abrasion and steel compressed air connections suitable for high flow rates.**
- **Pivoted bracket for wall mounting and the wall or ceiling.**

Hose reel for compressed air. Sturdy hose in bright orange **signal colour**. Ensures safe handling.

Supplied with:

Supplied with GARANT steel safety coupling and coupling adaptor.

Note:

See No. 080270 – 080272 for suitable safety couplings.

Technical description

Colour of housing	blue
Material of the housing	Plastic
usable hose length	10 m

Hose external Ø	12 mm
Material of hose	Polyurethane
Connection outlet	1/4 in
SCS automatic roll-up drum	yes
Hose internal Ø	8 mm
Colour of hose	orange
maximum operating pressure	16 bar
Body depth	190 mm
Body width	310 mm
Body height	406 mm
suitable for	Compressed air
Type of product	Hose reel

Accessories

Safety couplingInternal thread Connection internal thread 1/4 in	080271 1/4
Safety couplingHose connection Hose connection internal Ø (nominal bore) 11 mm	080272 11
Hose reel spare parts Type 7	080081 7
Safety couplingInternal thread Connection internal thread 1/2 in	080271 1/2
Safety couplingExternal thread Connection external thread 1/2 in	080270 1/2
Safety couplingHose connection Hose connection internal Ø (nominal bore) 8 mm	080272 8
Hose reel spare parts Type 11	080081 11
Hose reel spare parts Type 1	080081 1
Hose reel spare parts Type 4	080081 4
Safety couplingExternal thread Connection external thread 1/4 in	080270 1/4

Hose reel spare parts Type 13	080081 13
Safety couplingInternal thread Connection internal thread 3/8 in	080271 3/8
Hose reel spare parts Type 15	080081 15
Safety couplingHose connection Hose connection internal Ø (nominal bore) 13 mm	080272 13
Safety couplingExternal thread Connection external thread 3/8 in	080270 3/8