

**Garant**
**Safety hose reel, plastic casing Compressed air, usable hose length: 15m**


## Order data

Order number	080078 15
GTIN	4062406284688
Item class	01A

## Description

### Version:

- **Safety hose reel with high-impact enclosed plastic casing for use in dirty and dusty environments.**
- **Hose guide and controlled retraction system.**
- **Integral stop ball.**
- **PU hose with high resistance to abrasion and steel compressed air connections suitable for high flow rates.**
- **Pivoted bracket for wall mounting and the wall or ceiling.**

Hose reel for compressed air. Sturdy hose in bright orange **signal colour**. Ensures safe handling.

### Supplied with:

Supplied with GARANT steel safety coupling and coupling adaptor.

### Note:

See No. 080270 – 080272 for suitable safety couplings.

## Technical description

Colour of housing	blue
SCS automatic roll-up drum	yes
usable hose length	15 m
Material of the housing	Plastic

maximum operating pressure	16 bar
Hose internal Ø	9.5 mm
Colour of hose	orange
Material of hose	Polyurethane
Connection outlet	3/8 in
Hose external Ø	13.5 mm
Body width	490 mm
Body height	409 mm
Body depth	190 mm
suitable for	Compressed air
Type of product	Hose reel

## Accessories

Safety couplingInternal thread Connection internal thread 1/4 in	080271 1/4
Hose reel spare parts Type 8	080081 8
Safety couplingHose connection Hose connection internal Ø (nominal bore) 11 mm	080272 11
Safety couplingExternal thread Connection external thread 1/2 in	080270 1/2
Hose reel spare parts Type 15	080081 15
Safety couplingHose connection Hose connection internal Ø (nominal bore) 8 mm	080272 8
Safety couplingHose connection Hose connection internal Ø (nominal bore) 13 mm	080272 13
Safety couplingInternal thread Connection internal thread 3/8 in	080271 3/8
Hose reel spare parts Type 2	080081 2
Safety couplingInternal thread Connection internal thread 1/2 in	080271 1/2

Safety coupling External thread Connection external thread 3/8 in	080270 3/8
Hose reel spare parts Type 14	080081 14
Safety coupling External thread Connection external thread 1/4 in	080270 1/4
Hose reel spare parts Type 5	080081 5
Hose reel spare parts Type 12	080081 12