

Garant**Safety hose reel, plastic casing Water, usable hose length: 15m**

Order data

Order number	080079 15
GTIN	4062406284695
Item class	01A

Description

Version:

- **Safety hose reel with high-impact enclosed plastic casing for use in dirty and dusty environments.**
- **Hose guide and controlled retraction system.**
- **Integral stop ball.**
- **PU hose with high resistance to abrasion and steel compressed air connections suitable for high flow rates.**
- **Pivoted bracket for wall mounting and the wall or ceiling.**

Water hose reel for liquids. Hose colour steel blue.

Supplied with:

Includes coupling adaptor.

Note:

For water coupling see No. 080149 1/2.

Technical description

maximum operating pressure	16 bar
Colour of housing	blue
usable hose length	15 m

Colour of hose	blue
SCS automatic roll-up drum	yes
Material of the housing	Plastic
Hose external Ø	13.5 mm
Hose internal Ø	9.5 mm
Connection outlet	1/2 in
Material of hose	Polyurethane
Body depth	190 mm
Body height	409 mm
Body width	490 mm
suitable for	Liquids
Type of product	Hose reel

Accessories

Hose reel spare parts Type 12	080081 12
Hose reel spare parts Type 15	080081 15
Hose reel spare parts Type 14	080081 14
Hose reel spare parts Type 3	080081 3
Hose reel spare parts Type 6	080081 6
Hose reel spare parts Type 9	080081 9