

**Garant****Safety hose reel, plastic casing Water, usable hose length: 15m**

## Order data

Order number	080079 15
GTIN	4062406284695
Item class	01A

## Description

### Version:

- **Safety hose reel with high-impact enclosed plastic casing for use in dirty and dusty environments.**
- **Hose guide and controlled retraction system.**
- **Integral stop ball.**
- **PU hose with high resistance to abrasion and steel compressed air connections suitable for high flow rates.**
- **Pivoted bracket for wall mounting and the wall or ceiling.**

Water hose reel for liquids. Hose colour steel blue.

### Supplied with:

Includes coupling adaptor.

### Note:

For water coupling see No. 080149 1/2.

## Technical description

maximum operating pressure	16 bar
Colour of housing	blue
usable hose length	15 m

Colour of hose	blue
SCS automatic roll-up drum	yes
Material of the housing	Plastic
Hose external Ø	13.5 mm
Hose internal Ø	9.5 mm
Connection outlet	1/2 in
Material of hose	Polyurethane
Body depth	190 mm
Body height	409 mm
Body width	490 mm
suitable for	Liquids
Type of product	Hose reel

---

## Accessories

Hose reel spare parts Type 12	080081 12
Hose reel spare parts Type 14	080081 14
Hose reel spare parts Type 15	080081 15
Hose reel spare parts Type 3	080081 3
Hose reel spare parts Type 6	080081 6
Hose reel spare parts Type 9	080081 9