

Garant**Safety cable reel, Type: 15****Order data**

Order number	081198 15
GTIN	4062406284701
Item class	01A

Description**Version:**

Cable reel with **guided automatic draw-in and roll-up, with multiple stop points per revolution**. High-impact enclosed **plastic housing**. Thermal **overload cut-out**, sturdy H07RN-F neoprene cable with connection point.

Easy to mount on the wall or ceiling, with **180° pivoting range**.

Function:

IP44: Protected against splashed water from all directions and protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away.

Application:

Improved ergonomics by relieving cable tension, and for ensuring tidiness and avoiding the risk of accidents and injuries due to cables lying on the ground.

Note:

For spring return hose reels see No. 080066 to 080079.

Technical description

Length	496 mm
Width	192 mm

Cable structure	3G1.5
Cable length	15 m
Height	401 mm
Rated power unrolled	2400 W
Material cable	Neoprene rubber
Cable class	H07RN-F
Nominal voltage	250 V
IP Index of Protection	IP 44
Power supply	Mains operated
Type of product	Cable reel

Accessories

Hose reel spare parts Type 16	080081 16
Hose reel spare parts Type 10	080081 10
Hose reel spare parts Type 12	080081 12
Hose reel spare parts Type 14	080081 14