

**Garant**
**Boring bar carbide, right-hand, Shank  $\varnothing$  / insert size: 16/07mm**

**Order data**

Order number	261332 16/07
GTIN	4062406283575
Item class	21T

**Technical description**

Insert size	7 mm
Neck width $L_4$	14.5 mm
suitable indexable insert	VC.. 0702..
Clamping height $L_2$	15 mm
Centre offset $L_3$	11 mm
ISO code toolholder	E16M SVLCR/L07
Minimum pre-drill $\varnothing D_{\min}$	19.5 mm
Overall length L	150 mm
Pack of insert screws	269028 26
Head length $L_1$	55 mm
Setting angle $\kappa$	95 degrees
Usable depth T	5 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------