

**Garant**
**Boring bar carbide, left-hand, Shank  $\varnothing$  / insert size: 8/05mm**

**Order data**

Order number	261333 8/05
GTIN	4062406283582
Item class	21T

**Technical description**

Insert size	5 mm
Head length $L_1$	26 mm
Neck width $L_4$	6 mm
Overall length $L$	80 mm
ISO code toolholder	E08F SVLCR/L05
Pack of insert screws	269028 27
Setting angle $\kappa$	95 degrees
Clamping height $L_2$	7.5 mm
Minimum pre-drill $\varnothing D_{\min}$	9.2 mm
Centre offset $L_3$	5 mm
suitable indexable insert	VC.. 0501..
Usable depth $T$	3 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 26	269028 26
------------------------------	-----------