

Garant
Boring bar carbide, right-hand, Shank \varnothing / insert size: 12/07mm

Order data

| | |
|--------------|---------------|
| Order number | 261332 12/07 |
| GTIN | 4062406283568 |
| Item class | 21T |

Technical description

| | |
|--|----------------|
| Overall length L | 125 mm |
| Neck width L ₄ | 9 mm |
| Insert size | 7 mm |
| Minimum pre-drill $\varnothing D_{\min}$ | 15.5 mm |
| Head length L ₁ | 40 mm |
| Clamping height L ₂ | 11 mm |
| suitable indexable insert | VC.. 0702.. |
| Pack of insert screws | 269028 26 |
| Setting angle κ | 95 degrees |
| Centre offset L ₃ | 9 mm |
| ISO code toolholder | E12K SVLCR/L07 |
| Usable depth T | 6 mm |
| Shank $\varnothing D_s$ | 12 mm |
| Standard | Works standard |
| Application type | right-hand |
| Boring depth up to | 8xD |
| Tool material | Carbide |

| | |
|-----------------|-------------------------------|
| Through-coolant | yes |
| Application | Internal longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|------------------------------|-----------|
| Set of insert screws Type 27 | 269028 27 |
|------------------------------|-----------|