

**Garant**
**Boring bar carbide, right-hand, Shank  $\varnothing$  / insert size: 12/07mm**

**Order data**

Order number	261336 12/07
GTIN	4062406285548
Item class	21T

**Technical description**

ISO code toolholder	E12K SVVCR/L07
Pack of insert screws	269028 26
Overall length L	125 mm
Neck width L <sub>4</sub>	9 mm
Clamping height L <sub>2</sub>	11 mm
Centre offset L <sub>3</sub>	9 mm
Head length L <sub>1</sub>	40 mm
Setting angle $\kappa$	72.5 degrees
Insert size	7 mm
Minimum pre-drill $\varnothing D_{\min}$	15.5 mm
suitable indexable insert	VC.. 0702..
Usable depth T	6 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8×D
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------