

**Garant**
**Boring bar carbide, left-hand, Shank  $\varnothing$  / insert size: 16/07mm**

**Order data**

Order number	261333 16/07
GTIN	4062406285517
Item class	21T

**Technical description**

Overall length L	150 mm
Insert size	7 mm
suitable indexable insert	VC.. 0702..
Pack of insert screws	269028 26
Setting angle $\kappa$	95 degrees
Clamping height L <sub>2</sub>	15 mm
ISO code toolholder	E16M SVLCR/L07
Centre offset L <sub>3</sub>	11 mm
Minimum pre-drill $\varnothing D_{\min}$	19.5 mm
Head length L <sub>1</sub>	55 mm
Neck width L <sub>4</sub>	14.5 mm
Usable depth T	5 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------