

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 16/07mm

Order data

Order number	261337 16/07
GTIN	4062406285593
Item class	21T

Technical description

Setting angle κ	72.5 degrees
Neck width L_4	12.9 mm
ISO code toolholder	E16M SVVCR/L07
Head length L_1	55 mm
Clamping height L_2	15 mm
Overall length L	150 mm
Insert size	7 mm
Pack of insert screws	269028 26
suitable indexable insert	VC.. 0702..
Centre offset L_3	11 mm
Minimum pre-drill $\varnothing D_{\min}$	19.5 mm
Usable depth T	6 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8×D
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------