

**Garant**
**Boring bar steel, right-hand, Shank Ø / insert size: 10/07mm**

**Order data**

Order number	261356 10/07
GTIN	4062406285692
Item class	21T

**Technical description**

Overall length L	100 mm
Insert size	7 mm
Neck width L <sub>4</sub>	6.8 mm
Minimum pre-drill Ø D <sub>min</sub>	12.5 mm
ISO code toolholder	A10H SVXCR/L07
Clamping height L <sub>2</sub>	9 mm
Head length L <sub>1</sub>	22 mm
Pack of insert screws	269028 26
Centre offset L <sub>3</sub>	7 mm
Setting angle κ	113 degrees
suitable indexable insert	VC.. 0702..
Usable depth T	3 mm
Shank Ø D <sub>s</sub>	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------