

Garant
Boring bar steel, right-hand, Shank Ø / insert size: 16/07mm

Order data

Order number	261356 16/07
GTIN	4062406285715
Item class	21T

Technical description

Overhang L_1	48 mm
Centre offset L_3	11 mm
Clamping height L_2	15 mm
Minimum pre-drill $\varnothing D_{\min}$	19.5 mm
ISO code toolholder	A16M SVXCR/L07
Overall length L	150 mm
Insert size	7 mm
Setting angle κ	113 degrees
Pack of insert screws	269028 26
suitable indexable insert	VC.. 0702..
Usable depth T	3 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

Set of insert screws Type 27

269028 27