

Garant
Boring bar steel, right-hand, Shank Ø / insert size: 8/05mm

Order data

| | |
|--------------|---------------|
| Order number | 261356 8/05 |
| GTIN | 4062406285685 |
| Item class | 21T |

Technical description

| | |
|--|----------------|
| Neck width L_4 | 6 mm |
| Head length L_1 | 15 mm |
| Clamping height L_2 | 7.5 mm |
| Overall length L | 80 mm |
| Pack of insert screws | 269028 27 |
| ISO code toolholder | A08F SVXCR/L05 |
| Minimum pre-drill $\varnothing D_{\min}$ | 9.2 mm |
| Insert size | 5 mm |
| Setting angle κ | 113 degrees |
| suitable indexable insert | VC.. 0501.. |
| Centre offset L_3 | 5 mm |
| Usable depth T | 3 mm |
| Shank $\varnothing D_s$ | 8 mm |
| Standard | Works standard |
| Application type | right-hand |
| Boring depth up to | 3xD |
| Through-coolant | yes |

| | |
|-----------------|-------------------------------|
| Application | Internal longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|------------------------------|-----------|
| Set of insert screws Type 26 | 269028 26 |
|------------------------------|-----------|