

Garant
Boring bar steel, left-hand, Shank \varnothing / insert size: 16/07mm

Order data

Order number	261357 16/07
GTIN	4062406285753
Item class	21T

Technical description

Overall length L	150 mm
suitable indexable insert	VC.. 0702..
ISO code toolholder	A16M SVXCR/L07
Overhang L ₁	48 mm
Centre offset L ₃	11 mm
Minimum pre-drill $\varnothing D_{\min}$	19.5 mm
Insert size	7 mm
Setting angle κ	113 degrees
Pack of insert screws	269028 26
Clamping height L ₂	15 mm
Usable depth T	3 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring bar

Accessories

Set of insert screws Type 27

269028 27