

Garant
Boring bar carbide, left-hand, Shank \varnothing / insert size: 10/07mm

Order data

| | |
|--------------|---------------|
| Order number | 261369 10/07 |
| GTIN | 4062406285814 |
| Item class | 21T |

Technical description

| | |
|--|----------------|
| Insert size | 7 mm |
| Setting angle κ | 113 degrees |
| ISO code toolholder | E10H SVXCR/L07 |
| suitable indexable insert | VC.. 0702.. |
| Head length L_1 | 32 mm |
| Centre offset L_3 | 7 mm |
| Neck width L_4 | 6.8 mm |
| Clamping height L_2 | 9 mm |
| Overall length L | 100 mm |
| Pack of insert screws | 269028 26 |
| Minimum pre-drill $\varnothing D_{\min}$ | 12.5 mm |
| Usable depth T | 3 mm |
| Shank $\varnothing D_s$ | 10 mm |
| Standard | Works standard |
| Application type | left-hand |
| Boring depth up to | 8xD |
| Tool material | Carbide |

| | |
|-----------------|-------------------------------|
| Through-coolant | yes |
| Application | Internal longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|------------------------------|-----------|
| Set of insert screws Type 27 | 269028 27 |
|------------------------------|-----------|