

**Garant**
**Boring bar carbide, left-hand, Shank  $\varnothing$  / insert size: 12/07mm**

**Order data**

Order number	261369 12/07
GTIN	4062406285821
Item class	21T

**Technical description**

suitable indexable insert	VC.. 0702..
ISO code toolholder	E12K SVXCR/L07
Setting angle $\kappa$	113 degrees
Head length $L_1$	40 mm
Centre offset $L_3$	9 mm
Insert size	7 mm
Minimum pre-drill $\varnothing D_{\min}$	15.5 mm
Pack of insert screws	269028 26
Clamping height $L_2$	11 mm
Overall length $L$	125 mm
Overhang $L_1$	96 mm
Usable depth $T$	3 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------