

Garant
Boring bar carbide, right-hand, Shank \varnothing / insert size: 12/07mm

Order data

Order number	261368 12/07
GTIN	4062406285784
Item class	21T

Technical description

Setting angle κ	113 degrees
Head length L_1	40 mm
Overall length L	125 mm
Centre offset L_3	9 mm
Clamping height L_2	11 mm
ISO code toolholder	E12K SVXCR/L07
Insert size	7 mm
Minimum pre-drill $\varnothing D_{\min}$	15.5 mm
suitable indexable insert	VC.. 0702..
Pack of insert screws	269028 26
Overhang L_1	96 mm
Usable depth T	3 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------