

Garant
Boring bar carbide, right-hand, Shank \varnothing / insert size: 16/07mm

Order data

Order number	261368 16/07
GTIN	4062406285791
Item class	21T

Technical description

Overall length L	150 mm
Clamping height L ₂	15 mm
ISO code toolholder	E16M SVXCR/L07
Setting angle κ	113 degrees
Pack of insert screws	269028 26
Insert size	7 mm
Overhang L ₁	128 mm
Minimum pre-drill $\varnothing D_{\min}$	19.5 mm
Centre offset L ₃	11 mm
suitable indexable insert	VC.. 0702..
Head length L ₁	55 mm
Usable depth T	3 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------