



Steplessly extendable telescopic precision ratchet 1/2 inch, Type: 1/2



Order data

Order number	640291 1/2
GTIN	4000896233076
Item class	630

Description

Version:

Material selection and special forging method guarantee optimal functioning and long life. Fixing is performed by the locking ring. With reversing lever for right-hand and left-hand threads. Steplessly extendable from 414 – 614 mm length. Reversible fine-tooth ratchet with 90 teeth. Maximum permissible torque 1000 Nm.

Standard:

Außenvierkant nach **DIN 3120-A 12,5** mit federnder Kugel.

Suitable for:

Manual use.

Technical description

Square drive	1/2 in
overall length	414 - 614 mm
No. of teeth	90
stepless pull-out	yes
Type of product	Ratchet