

**Garant**
**Boring bar carbide, left-hand, Shank  $\varnothing$  / insert size: 8/05mm**


## Order data

Order number	261337 8/05
GTIN	4062406285845
Item class	21T

## Technical description

ISO code toolholder	E08F SVVCR/L05
Clamping height $L_2$	7.5 mm
Minimum pre-drill $\varnothing D_{\min}$	10.2 mm
suitable indexable insert	VC.. 0501..
Neck width $L_4$	6 mm
Overall length $L$	80 mm
Pack of insert screws	269028 27
Setting angle $\kappa$	72.5 degrees
Centre offset $L_3$	5.5 mm
Head length $L_1$	26 mm
Insert size	5 mm
Usable depth $T$	3,5 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8×D
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 26	269028 26
------------------------------	-----------