

**Garant****Boring bar carbide, right-hand, Shank  $\varnothing$  / insert size: 8/05mm****Order data**

Order number	261368 8/05
GTIN	4062406285876
Item class	21T

**Technical description**

Head length $L_1$	26 mm
Centre offset $L_3$	5 mm
suitable indexable insert	VC.. 0501..
Insert size	5 mm
Pack of insert screws	269028 27
Setting angle $\kappa$	113 degrees
Clamping height $L_2$	7.5 mm
Overall length $L$	80 mm
ISO code toolholder	E08F SVXCR/L05
Minimum pre-drill $\varnothing D_{\min}$	9.2 mm
Neck width $L_4$	6 mm
Usable depth $T$	3 mm
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 26	269028 26
------------------------------	-----------