

Garant GRIDLINE

## Trough set, 20×20G, Drawer front height / type: 50/1



### Order data

Order number	950310 50/1
GTIN	4062406285890
Item class	9GB

### Description

#### Version:

Troughs and divider plates of plastic. Troughs slotted on the inside for division using divider plates.

Dividing material fills a complete drawer 20×20G.

#### Suitable for:

Drawers 20×20G.

#### Content:

Troughs 1K No. 951415: 6 × size 6×6/4; 3 × size 6×8/4; 2 × size 2×6/1; 1 × size 2×8/1

Troughs divider plates (10 pcs.) No. 951275: 4 × size C

### Technical description

suitable for drawer front height	50 mm
suitable for drawer front height	100 mm
suitable for drawer front height	75 mm
suitable for drawer front height	150 mm
suitable for drawer front height	125 mm
suitable for drawer front height	300 mm
suitable for drawer front height	250 mm
suitable for drawer front height	200 mm
Trough height	25 mm

suitable for drawers usable width	500 mm
Drawer usable area in G	20×20
suitable for drawers usable width in G	20
suitable for drawers usable depth in G	20
suitable for drawers usable depth	500 mm
Material	Plastic
suitable from drawer front height	≥ 50 mm
Depth	500 mm
Width	500 mm
Height	25 mm
Depth in G	20
Width in G	20
Weight	1.142 kg
Product name attribute	20×20G
Type of product	Drawer trough

## Accessories

Trough height 25 mm1K Width×depth in G / type 6X6/4	951415 6X6/4
Trough divider platesSet 10 pieces Type C	951275 C
Trough height 25 mm1K Width×depth in G / type 6X8/4	951415 6X8/4
Trough height 25 mm1K Width×depth in G / type 2X6/1	951415 2X6/1
Trough height 25 mm1K Width×depth in G / type 2X8/1	951415 2X8/1