

Garant GRIDLINE

## Trough set, 36×20G, Drawer front height / type: 50/3



### Order data

Order number	950410 50/3
GTIN	4062406286569
Item class	9GB

### Description

#### Version:

Troughs and divider plates of plastic. Troughs slotted on the inside for division using divider plates.

Dividing material fills a complete drawer 36×20G.

#### Suitable for:

Drawers 36×20G.

#### Content:

Troughs 1K No. 951415: 2 × size 6×6/4; 1 × size 6×8/4; 4 × size 6×6/3; 6 × size 6×6/2; 3 × size 6×8/2; 2 × size 6×8/3

Troughs divider plates (10 pcs.) No. 951275: 2 × size C; 2 × size B; 2 × size A

### Technical description

suitable for drawers usable depth in G	20
Drawer usable area in G	36×20
suitable for drawers usable width	900 mm
suitable for drawer front height	50 mm
suitable for drawer front height	100 mm
suitable for drawer front height	75 mm
suitable for drawer front height	150 mm
suitable for drawer front height	125 mm

suitable for drawer front height	250 mm
suitable for drawer front height	200 mm
suitable for drawer front height	300 mm
suitable for drawers usable depth	500 mm
Trough height	25 mm
suitable for drawers usable width in G	36
Material	Plastic
suitable from drawer front height	≥ 50 mm
Height	25 mm
Depth in G	20
Width in G	36
Width	900 mm
Depth	500 mm
Weight	1.868 kg
Product name attribute	36x20G
Type of product	Drawer trough

## Accessories

Trough height 25 mm1K Width×depth in G / type 6X6/2	951415 6X6/2
Trough height 25 mm1K Width×depth in G / type 6X6/4	951415 6X6/4
Trough height 25 mm1K Width×depth in G / type 6X8/2	951415 6X8/2
Trough height 25 mm1K Width×depth in G / type 6X8/4	951415 6X8/4
Trough divider platesSet 10 pieces Type C	951275 C
Trough height 25 mm1K Width×depth in G / type 6X6/3	951415 6X6/3
Trough height 25 mm1K Width×depth in G / type 6X8/3	951415 6X8/3
Trough divider platesSet 10 pieces Type B	951275 B
Trough divider platesSet 10 pieces Type A	951275 A