

Garant
HCT digital caliper IP67 with Bluetooth, Measuring range: 300 mm

Order data

| | |
|--------------|---------------|
| Order number | 412780 300 |
| GTIN | 4062406286736 |
| Item class | 41A |

Description
Version:

Digital calipers to IP67 with **Bluetooth**. **Easy-to-read, high-contrast LCD display with 11.5mm character height**. Very long battery running time due to modern energy-efficient measurement system. The system switches automatically into power-saving mode after 10 minutes; moving the caliper reactivates it. There is no loss of the measurement value or zero point.

2-component body with **non-slip Haptoprene surface**. The caliper is resistant to water, coolant, oil, and dust. The measuring faces are precision-lapped.

For ease of use, the optional Hoffmann Group Connected Tools (HCT) app for Android and iOS is available free of charge. without depth gauge

Advantage:
HCT – Hoffmann Group Connected Tools

Advantages of wireless transmission with Bluetooth:

- **Simple data transmission: At the push of a button the measuring result is transmitted directly to your PC application (such as Excel or Word) or to your mobile phone - no dongle necessary.**
- **Freedom of movement: No messy data transmission cables.**
- **Independence of location: Measurements can be performed directly to the machine and transmitted by radio to your application.**
- **Reliable data transmission: No read errors and transmission errors - multiple measuring devices can be linked together.**

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Standard:

to manufacturer's standard

Supplied with:

1 battery No. 081560 size CR2032.

Spare part:

Battery holder No. 412237 size B.

Packaging: sturdy box

Standard: Manufacturer's standard

Reversible reading: mm / inch

IP Index of Protection: IP 67

Wireless application: HCT Mobile App

Wireless application: HID (Human Interface Device)

Calibration: A1

Scale divisions: 0.01 mm

Scale divisions: 0.0005 in

Error limit: 0.03 mm

Jaw length: 65 mm

Wireless application: HCT Mobile App

Wireless application: HID (Human Interface Device)

Technical description

| | |
|--|-------------------------|
| Measurement value and zero point preserved after reactivation from standby | yes |
| Article no of the battery / rechargeable battery fitted | 081560 CR2032 |
| Battery type | Button cell |
| Measuring range | 0 - 300 mm |
| Standard | Manufacturer's standard |
| Auto switch-off | yes |
| Scale divisions | 0.0005 in |
| Digit height LCD display | 11.5 mm |
| Number of batteries contained | 1 |
| Series | HCT |
| Reversible reading | mm / inch |
| Automatic stand-by circuit. | yes |
| Error limit | 0.03 mm |
| Jaw length | 65 mm |
| Calibration | A1 |
| Scale divisions | 0.01 mm |

| | |
|------------------------|------------------------------|
| IP Index of Protection | IP 67 |
| Power supply | Battery-powered |
| Wireless application | HCT Mobile App |
| Wireless application | HID (Human Interface Device) |
| International size | CR2032 |
| Interface | Bluetooth interface |
| Measurement technology | digital |
| Material | Stainless steel, INOX |
| all parts | hardened |
| Packaging | sturdy box |
| Type of product | Universal calipers |

Services

| | |
|--|------------|
| Labelling laser-etched Type | 018940 |
| Calibration Calipers / depth gauges maximum measuring range 300 mm | 011030 300 |
| DAkkS calibration Calipers / depth gauges maximum measuring range 300 mm | 011050 300 |
| Calibration Calipers / depth gauges maximum measuring range 300 mm | 021000 300 |
| DAkkS calibration Calipers / depth gauges maximum measuring range 300 mm | 021010 300 |

Accessories

| | |
|---|---------------|
| Button cell / special battery Battery type CR2032 | 081560 CR2032 |
| Screw for depth gauge holder | 412236 |
| Cover for vernier calipers Type B | 412237 B |