

 Mahr**Digital caliper MarCal i-wi with measuring tips, Measuring range: 750mm****Order data**

Order number	415321 750
GTIN	4059192062118
Item class	43A

Description**Version:**

Direct reading from large and clear digital display. Precision lapped measuring faces. The REFERENCE measuring system saves and retains the set zero position, even after being switched on again. The lock function prevents measurement errors arising from accidentally touching the control buttons.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size CR2032.

Optional extras:

Data cable No. 498940.

i-wi radio receiver No. 498912

Technical description

Article no of the battery / rechargeable battery fitted	081560 CR2032
Calibration	A1
Number of batteries contained	1
Scale divisions	0.01 mm
Reversible reading	mm / inch
Error limit	0.05 mm

Measuring range	0 - 750 mm
Jaw length	150 mm
Internal jaw Ø	20 mm
Scale divisions	0.0005 in
IP Index of Protection	IP 65
Power supply	Battery-powered
Wireless application	Manufacturer's software
Standard	Works standard
Interface	MAHR i-wi radio system
Measured value saving	MAHR reference-lock system
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Workshop calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 1000 mm	021000 1000
DAkkS calibrationCalipers / depth gauges maximum measuring range 1000 mm	021010 1000

Accessories

Connection cablesimplex with data key Type D2	498940 D2
Connection cablesimplex with data key Type R2	498940 R2
Connection cablesimplex with data key Type USB2	498940 USB2
Button cell / special battery Battery type CR2032	081560 CR2032