

Mitutoyo**Digital external micrometer IP65 with data output, Measuring range:
125-150mm****Order data**

Order number	421525 125-150
GTIN	4946368695433
Item class	44A

Description**Version:**

Error limits more accurate than the requirements of **DIN 863**.

Extra large LCD display (7.5 mm high) for quick, error-free reading, keyboard lock.

Carbide-tipped measuring faces.

Shock-proof version.

Measuring spindle hardened and ground.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Supplied with:

1 battery No. 081560 size 357, 1 setting standard from size 25 -50.

Optional extras:

No. 421525 and 421527. Data cable No. 497445.

Technical description

Number of batteries contained	1
Scale divisions	0.001 mm
Calibration	B2
Error limit	3 µm

Measuring range	125 - 150 mm
Spindle pitch	0.5 mm
Article no of the battery / rechargeable battery fitted	081560 357
Spindle Ø	6.35 mm
IP Index of Protection	IP 65
Power supply	Battery-powered
Standard	Manufacturer's standard
Interface	USB interface
Interface	USB interface
Measurement technology	digital
Packaging	sturdy box
Type of product	External tube micrometer

Services

DAkkS calibration External micrometer including setting dimension maximum measuring range 200 mm	022050 200
Calibration External micrometer including setting dimension maximum measuring range 200 mm	022040 200