

**LESSMANN®**  
THE GERMAN BRUSH COMPANY
**Tube brush Waved steel wire 0.15 mm, Brush Ø: 8mm**

**Order data**

Order number	577980 8
GTIN	4017359004241
Item class	57L

**Description**
**Version:**

Internal brushes with galvanised twisted wire core and plain helix of bristles. Bristles of waved wire, overall length 115 mm. Bristle length 80 mm long with crimped-on M6 threaded nipple.

**Application:**

For cleaning pipes, gratings, sleeves, heat exchangers, and cylinders. For use in machines (only clockwise rotation), use thread adapter No. 577990.

**Technical description**

Brush Ø D <sub>1</sub>	8 mm
Overall length L	115 mm
Brush material	Steel wire
Adapter	Threaded nipple
Bristle thickness	0.15 mm
Type of product	Tube brush

**Accessories**

Extension for tube brushes with M6 threaded nipple Thread M6	577993 M6
	577995 M6

Plastic handle for tube brushes with M6 threaded nipple  
Thread M6

M6 thread adapter, internal thread Shank Ø 6 mm Thread  
M6

577990 M6