

LESSMANN®
THE GERMAN BRUSH COMPANY**Tube brush Waved steel wire 0.15 mm, Brush Ø: 15mm****Order data**

Order number	577980 15
GTIN	4017359013755
Item class	57L

Description**Version:**

Internal brushes with galvanised twisted wire core and plain helix of bristles. Bristles of waved wire, overall length 115 mm. Bristle length 80 mm long with crimped-on M6 threaded nipple.

Application:

For cleaning pipes, gratings, sleeves, heat exchangers, and cylinders. For use in machines (only clockwise rotation), use thread adapter No. 577990.

Technical description

Brush Ø D ₁	15 mm
Overall length L	115 mm
Brush material	Steel wire
Adapter	Threaded nipple
Bristle thickness	0.15 mm
Type of product	Tube brush

Accessories

M6 thread adapter, internal thread Shank Ø 6 mm Thread M6	577990 M6
	577993 M6

Extension for tube brushes with M6 threaded nipple
Thread M6

Plastic handle for tube brushes with M6 threaded nipple
Thread M6

577995 M6